

PORTABLE TYPE ULTRASONIC FLOWMETER Portaflow-C



Vastly improved Portafiow-C






Provided with printer for screen hard copy



stored in a SD memory card Saves instantaneous value, total value, error information

Computation function of consumed heat quantity: This function calculates the heat quantity received and sent with liquid (water) in cooling Consumed heat quantity $q = K \cdot Q \cdot (T1-T2)$ K: heat quantity and heating. conversion factor (For heating K = 4.123) Temperature sensor



T2: Temperature of the heating medium of the receiving side Q: Flow rate of the heating medium

Large easy-to-read LCD display








TRANSIT TIME/RECEPT

PROFILE

LOGGER DATA

SD card archive date is playable on a PC

[Attached standard loader software]



Specifications

Application	Uniform liquid in which ultrasonic waves can propagateWater, hot-water, distilled water, alcohol, milk, ethanol, etc
Inner pipe diameter	13mm to φ6000mm (depending on the detector)
Fluid temperature	-40 to +200°C (depending on the detector)
Flow velocity range	0 to ±32m/s (±0.3m/s min.)
Measurement accuracy	±1.0% of rate(depending on the flow velocity)
Response time	1 sec.
Path	Transit time method (1 Path)
Display	Color graphic LCD with back light
Analog output signal	4 to 20mA DC (1 point)
Analog input signal	4 to 20mA DC / 1 to 5V DC (2 points)
Supply voltage	Built-in battery (In the fully charged condition, 12 hours of continuous operation is possible.)
Structure	Waterproof (IP64)
Size	210X120X65mm (without printer)
Weight	Approx. 1kg

	SD memory	It can be saved almost a year date by attached date
	card	standards (256MB)
	Serial communication	Transmission data (data stored in a SD memory card such as instantaneous value, total value, etc) • USB port is used • Transmission distance: 3 m max.
	Function	Damping time constant variable within 0 to 100 sec Instantaneous value display (10 digits) Various flow rate unit settable Total value display (10 digits) Various flow rate unit settable Consumed heat quantity computation Self diagnosis (diagnoses battery voltage drop and received waveform from the sensor) Flash memory (measurement parameter for pipe, fluid, sensor, etc) A number of registered sites: 32 Zero point adjustment (Set zero/Clear available) Bi-directional flow measurement Low flow cut (0 to 5m/s)
	Option	With printer: Display hard copy, periodic printing and logged data printing Flow velocity profile (Pulse Doppler method): Displays flow velocity profile of instantaneous value and average value



International Sales Div. Sales Group

Gate City Ohsaki, East Tower, 11-2, Osaki 1-chome, Shinagawa-ku, Tokyo 141-0032, Japan http://www.fujielectric.com

Phone: 81-3-5435-7280, 7281 Fax: 81-3-5435-7425 http://www.fujielectric.com/products/instruments/